

# **Technical Data Sheet**


# WIRELESS HIGH TEMPERATURE DATA LOGGER S-Radio Flexible



#### **Features**

- Real time monitoring data logger
- With different lengths rigid probe for penetration
- Completely food grade and waterproof
- All software calculate lethality value (F0, PU, A0 ecc.)
- Low battery consumption for an extended battery life
- User replaceable battery (software shows battery status)
- Very easy to deploy in any type of package
- Accredia (NIST equivalent) traceable calibration certificate included
- It is supported by the TS Manager software for validationcompatible with the FDA 21 CFR Part 11 and GAMP 5 regulations.
- Application for Sterilisation, Pasteurisation, Food and Beverage, Phamaceutical, Healthcare, Medical, Laboratories, Validation

### **Drawing**



#### **Technical data**

Temperature range: -40...+140°C

**Accuracy:**  $\pm$  0.1°C (within the calibration range)

Resolution: 0.01 °C

**Memory capacity:** 121,171 readings

Battery type: high temperature Lithium battery

**Battery life (@different interval):** more than 5 years @ 1 minute or 1 month @ 1 second (3,800,000 acquisitions @ 1 second step continuously (calculated time @25°C)). Storage or operation above +50°C

significantly reduces battery life.

Interval: 1s...24Hrs

Material: Strainless steel AISI316L, PEEK
Operate system: Windows 10, 11 (32/64 bit)

**Exporting:** PDF, Exel

**Dimension :** 76 x Φ30 mm (Body), 6 x Φ15 mm (Probe base), 300 x Φ4 mm

unit: mm (Probe Flexible)
Weight: 92q

Pressure resistance: 6 barG Protection type: IP68

## **Ordering code**

S-Radio Flexible



**50 :** Probe length 50 mm **XX :** Probe length 10...175mm

#### www.omi.co.th

Omega Measuring Instrument Co., Ltd.

Tel: 02-105-4676

Fax: 02-903-0080 ext. 6867 Email: info@omi.co.th Line: @omith

# **Application**









Sterilization process pasteurization process

Oven/Retori

\*Note: Furthermore, these process that are shown, please do not hesitate to contact us for consulting



# **Technical Data Sheet**

# WIRELESS HIGH TEMPERATURE DATA LOGGER S-Radio Flexible

# **Accessories (option)**

These are necessary equipments that using with products and increase efficiency.

to be programmed and downoaded at the same time.

**DiskInterface HS:** is the connection bay used in all model for downloading data and programming all models of high temperature data loggers



Universal Multibay: is the multiple connection bay used for downloading data and programming all models of high temperature data loggers. It allows to connect up to 5 data loggers of each supported model



**USB Radio Receiver:** is the receiver for wireless used in all S-Radio model for real time monitoring.



Autoclave special antenna: A special antenna to be inserted directly into the autoclave for optimal signal receiving is available. The antenna can be connected to any radio receiver instead of te standard antenna provided



**4-20mA Radio Receiver:** is the receiver that can be connected to the machinery's PLC



**S-RADIO-PLUG-3WAY**: The S-RADIO-PLUG-3WAY for addition a connecting of antenna. There are 2 of male plug for connecting.



**S-RADIO-CABLE-3**: The extension cable for Autoclave special antenna. It can extend a cable for receiving a signal from S-radio data logger. The cable length is 3 meters.



#### www.omi.co.th

Omega Measuring Instrument Co., Ltd.

Tel: 02-105-4676

Fax: 02-903-0080 ext. 6867 Email: info@omi.co.th Line: @omith



# **Technical Data Sheet**

# **WIRELESS HIGH TEMPERATURE DATA LOGGER S-Radio Flexible**

## **Accessories (option)**

These are necessary equipments that using with products and increase efficiency.

**TS17MU**: use to open data loggers for battery replacement.

Note : For all of sterilDisk model, need 2 items for opening For others model, need only 1 item for opening




TS10SPCRB: Battery and O-ring can be used in all type of S-Radio. if used below -30°C, battery life will be highly reduced



SPD Software (FREE): It allows to start the devices setting the start delay, mission du-

ration, notes. After download data are then displayed on graph, with zoom function, and table, exportable in Excel.



**TS Manager Software:** it allowed to do everything as a SPD software and has more functions such as multi-user, having login and password, Synchronized data table with statistics, etc. Downloadable from Tecnosoft website and works with its hardware protection key



## www.omi.co.th

Omega Measuring Instrument Co., Ltd.

Tel: 02-105-4676

Fax: 02-903-0080 ext. 6867 Email: info@omi.co.th Line: @omith